

MV-CH1010-10CM

101 MP CMOS Camera Link Area Scan Camera



GEN<I>CAM



Introduction

MV-CH1010-10CM camera adopts Sony® IMX461 sensor to provide high-quality images. It uses Camera Link interface to transmit non-compressed images in real time, and its max. frame rate can reach 8.1 fps in full resolution.

Key Feature

- Supports auto or manual adjustment of gain and exposure time, and manual adjustment of LUT and Gamma correction.
- Supports FFC correction function.
- Supports 16-bit ADC output with high acquisition accuracy and wide dynamic range.
- Provides camera with fan or TEC to meet different working temperature requirements.
- Supports configuration modes of Base, Medium, Full and 80-bit via the Camera Link interface.
- Compatible with Camera Link V2.0 Protocol, GenICam Standard, and the frame grabber software meeting with GenICam Protocol.


Available Model

- Mono camera with fan:
MV-CH1010-10CM-M72-NF
- Mono camera with TEC:
MV-CH1010-10CM-M72-TF

Applicable Industry

FPD detection, PCB AOI, file scanning, etc.

Sensor Quantum Efficiency



en.hikrobotics.com



Aremak Bilişim Teknolojileri
Endüstriyel Görüntü İşleme Çözümleri

Adres: ODTÜ Teknokent Bilişim ve İnovasyon Merkezi,
Mustafa Kemal Mahallesi, Dumlupınar Bulvarı No:280G,
İç Kapı No:1260, Çankaya, Ankara/Türkiye

W: www.aremak.com.tr
E: shop@aremak.com.tr
T: +908502551506

Specification

Model	MV-CH1010-10CM
Camera	
Sensor type	CMOS, rolling shutter
Sensor model	Sony® IMX461
Pixel size	3.76 µm × 3.76 µm
Sensor size	55 mm
Resolution	11648 × 8740
Max. frame rate	8.1 fps @11648 × 8740
Configuration mode	Base, Medium, Full, 80-bit
Tap geometry	2X_1Y, 4X_1Y, 8X_1Y, 10X_1Y
Tap number	2 Taps, 4 Taps, 8 Taps, 10 Taps
Pixel clock	40 MHz, 60 MHz, 70 MHz, 85 MHz
Dynamic range	78 dB
SNR	45 dB
Gain	0 dB to 36 dB
Exposure time	14 µs to 10 sec
Exposure mode	Off/Once/Continuous exposure mode, supports Global Reset
Mono/color	Mono
Pixel format	ADC 12-bit mode: Mono 8/10/12; ADC 16-bit mode: Mono 8/10/12/16
Binning	Supports 1 × 1, 1 × 2, 1 × 4, 2 × 1, 2 × 2, 2 × 4, 4 × 1, 4 × 2, 4 × 4
Decimation	Supports 1 × 1, 1 × 2, 1 × 4, 2 × 1, 2 × 2, 2 × 4, 4 × 1, 4 × 2, 4 × 4
Reverse image	Supports horizontal reverse image output
Electrical feature	
Data interface	Camera Link with SDR interface
Digital I/O	12-pin P10 connector provides power and I/O, including opto-isolated input × 1 (Line 0), opto-isolated output × 1 (Line 1), bi-directional non-isolated I/O × 1 (Line 2), and RS-232 × 1. Camera Link interface provides I/O (CC1/CC2/CC3/CC4)
Power supply	Camera with fan: 12 VDC to 24 VDC Camera with TEC: 24 VDC
Power consumption	Camera with fan: Typ. 14 W@24 VDC Camera with TEC non-cooling: Typ. 14 W@24 VDC Camera with TEC cooling: Typ. 48 W@24 VDC
Mechanical	
Lens mount	M72*0.75, flange back focal length 19.55 mm (0.8")
Dimension	Camera with fan: 90 mm × 90 mm × 71.5 mm (3.5" × 3.5" × 2.8") Camera with TEC: 100 mm × 100 mm × 87.2 mm (3.9" × 3.9" × 3.4")
Weight	Camera with fan: Approx. 790 g (1.7 lb.) Camera with TEC: Approx. 1.7 kg (3.7 lb.)
Ingress protection	IP40 (under proper lens installation and wiring)
Temperature	Working temperature: 0 °C to 50 °C (32 °F to 122 °F) Storage temperature: -30 °C to 70 °C (-22 °F to 158 °F)
Humidity	20% to 95% RH, non-condensing
General	
Client software	MVS or frame grabber software meetir
Operating system	32/64-bit Windows 7/10
Compatibility	Camera Link V2.0, GenICam
Certification	CE, RoHS, KC



Aremak Bilişim Teknolojileri


Endüstriyel Görüntü İşleme Çözümleri

Adres: ODTÜ Teknokent Bilişim ve İnovasyon Merkezi,
Mustafa Kemal Mahallesi, Dumlupınar Bulvarı No:280G,
İç Kapı No:1260, Çankaya, Ankara/Türkiye


W: www.aremak.com.tr
E: shop@aremak.com.tr
T: +908502551506

Dimension

Camera with fan:



Camera with TEC:



HIKROBOT

Hangzhou Hikrobot Co., Ltd.
en.hikrobotics.com

© Hangzhou Hikrobot Co., Ltd. All Rights Reserved.

Hangzhou Hikrobot does not tolerate any infringement. Any organization or individual may not imitate or reproduce in whole or in part of the content. The data herein is based on Hikrobot's internal evaluation. Actual data may vary depending on specific configuration and operating condition. The information herein is subject to change without notice. All the content has been checked conscientiously. Nevertheless, Hikrobot shall not be liable to damages resulting from errors, inconsistencies or omissions.



Aremak Biliřim Teknolojileri
Endüstriyel Görüntü İşleme Çözümleri

Adres: ODTÜ Teknokent Biliřim ve İnovasyon Merkezi,
Mustafa Kemal Mahallesi, Dumlupınar Bulvarı No:280G,
İç Kapı No:1260, Çankaya, Ankara/Türkiye

W: www.aremak.com.tr
E: shop@aremak.com.tr
T: +908502551506